



WXD202H

**Rocker for RJ45 socket gallery 2 modules pure-white**

**Technical properties**

**Architecture**

Type	Modular Jack
Fixing mode	Clipped

**Connectivity**

Outlet	with straight outlet
--------	----------------------

**Dimensions**

Depth	8.4 mm
Height	45 mm
Width	45 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	antibactérien
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

**Equipment**

Supporting plate / Supporting ring	without supporting ring
------------------------------------	-------------------------

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Application, usage	Communication technology
Range	gallery

Composition	other
With imprint	No