



WXD253D

**Rocker for TV+FM socket gallery 2 modules dune**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Connectivity**

Outlet with straight outlet

**Dimensions**

Depth 8.4 mm

Height 45 mm

Width 45 mm

**Capacity**

Number of sockets 1

**Materials**

Free area for finishing name dune

Surface appearance glossy

Type of surface treatment untreated

**Equipment**

Supporting plate / Supporting ring without supporting ring

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition other