



WXD253D

## Rocker for TV+FM socket gallery 2 modules dune

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Connectivity

Outlet	with straight outlet
--------	----------------------

#### Dimensions

Depth	8.4 mm
Height	45 mm
Width	45 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	dune
Surface appearance	glossy
Type of surface treatment	untreated

#### Equipment

Supporting plate / Supporting ring	without supporting ring
------------------------------------	-------------------------

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
Composition	other