



WXD253D

## Rocker for TV+FM socket gallery 2 modules dune

### Technical properties

#### Architecture

Fixing mode Clipped

#### Connectivity

Outlet with straight outlet

#### Dimensions

Depth 8.4 mm

Height 45 mm

Width 45 mm

#### Capacity

Number of sockets 1

#### Materials

Free area for finishing name dune

Surface appearance glossy

Type of surface treatment untreated

#### Equipment

Supporting plate / Supporting ring without supporting ring

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition other