



WXD256D

Rocker for TV+FM+SAT socket gallery 2 modules dune

Technical properties

Architecture

Fixing mode Clipped

Connectivity

Outlet with straight outlet

Dimensions

Depth 8.4 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name dune

Surface appearance glossy

Type of surface treatment untreated

Equipment

Supporting plate / Supporting ring without supporting ring

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other