



WXD744B

## VDI rocker gallery 2 modules pure

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	8.4 mm
-------	--------

Height	45 mm
--------	-------

Width	45 mm
-------	-------

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	pure
------------------------------	------

Colour	white
--------	-------

Type of surface treatment	untreated
---------------------------	-----------

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
---	----

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----