



WXD744D

VDI rocker gallery 2 modules dune

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	8.4 mm
Height	45 mm
Width	45 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	dune
Surface appearance	glossy
Type of surface treatment	untreated

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	other
With imprint	No