



WXF003

**2 way switch gallery InterBP with neutral 2 modules**

**Technical properties**

**Architecture**

Type of control unit	single rocker
Fixing mode	Clipped

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth	34 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

**Materials**

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	matt
Type of surface treatment	untreated

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	05
---	----

**Use conditions**

---

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

---

Range	gallery
Composition	Middle plate

---