



WXF015B

**Switch gallery 2 modules 2 poles 16A white**

**Technical properties**

**Architecture**

Type of control unit	single rocker
Fixing mode	Clipped

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 AX
---------------	-------

**Dimensions**

Depth	34 mm
Height	45 mm
Width	45 mm

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Polycarbonate (PC)
Type of surface treatment	untreated

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	07
---	----

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C