



WXF051



Automatic switch Gallery 3 wires

Technical properties

Functions

| | |
|----------------------|----|
| Remote operation | No |
| With switch function | No |

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 230 V |
| Frequency | 50/60 Hz |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Detection

| | |
|----------------------------|----------------------|
| Detection angle | 180 ° |
| Sensor type | detector of movement |
| Frontal detecting distance | 12 m |
| Side detecting distance | 8 m |

Lighting control

| | |
|-----------------------|--------------|
| Photocell sensitivity | 5 / 1000 Lux |
|-----------------------|--------------|

Connection

| | |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

Settings

| | |
|-----------|-----|
| Delay ON | 0 s |
| Delay OFF | 0 s |

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 03 |
| REACH conform | No |
| Halogen free | No |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|-------|---------|
| Range | gallery |
|-------|---------|