



WXF051



Automatic switch Gallery 3 wires

Technical properties

Functions

Remote operation	No
With switch function	No

Main electrical features

Nominal voltage	230 V
Frequency	50/60 Hz

Capacity

Number of modules for WA	2
--------------------------	---

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	12 m
Side detecting distance	8 m

Lighting control

Photocell sensitivity	5 / 1000 Lux
-----------------------	--------------

Connection

Type of connection	Screw connection
--------------------	------------------

Settings

Delay ON	0 s
Delay OFF	0 s

Safety

IK protection code against mechanical impacts	03
---	----

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Range	gallery
-------	---------