



WXF052

Automatic switch gallery 2 wires without neutral

Technical properties

Functions

Remote operation	No
With switch function	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Power

Maximum power per output for incandescent bulbs	20 / 300 W
---	------------

Capacity

Number of modules for WA	2
--------------------------	---

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	12 m
Side detecting distance	8 m

Lighting control

Photocell sensitivity	5 / 1000 Lux
-----------------------	--------------

Settings

Delay ON	0 s
Delay OFF	0 s

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Range	gallery
-------	---------