



WXF054

**Automatic switch gallery slave and staircase**

**Technical properties**

**Functions**

Remote operation	No
With switch function	No

**Main electrical features**

Nominal voltage	230 V
Frequency	50/60 Hz

**Capacity**

Number of modules for WA	2
--------------------------	---

**Detection**

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	12 m
Side detecting distance	8 m

**Lighting control**

Photocell sensitivity	5 / 1000 Lux
-----------------------	--------------

**Connection**

Type of connection	Screw connection
--------------------	------------------

**Settings**

Delay ON	0 s
Delay OFF	0 s

**Safety**

IK protection code against mechanical impacts	03
REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Range	gallery
-------	---------