



WXF061

## Push dimmer gallery eco lamps

### Technical properties

#### Architecture

Type of control unit	Push button
----------------------	-------------

#### Main electrical features

Nominal voltage	230 V
Frequency	50 Hz

#### Voltage

Operating voltage	230 V AC
-------------------	----------

#### Materials

Material	Polycarbonate (PC)
----------	--------------------

#### Installation, mounting

Mounting type	flush-mounted
Installation mode	for catch fixing

#### Connection

Type of load	universal
Conductor cross-section	1.5...2.5 mm <sup>2</sup>
Type of connection	Screw connection

#### Equipment

Substation input	Yes
Dimming principle	phase cut-on or cut-off according to load type, self-learning

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C