



WXF061

Push dimmer gallery eco lamps

Technical properties

Architecture

Type	Halogen
Type of control unit	Push button

Main electrical features

Nominal voltage	230 V
Nominal voltage	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V AC
-------------------	----------

Materials

Material	polycarbonate
----------	---------------

Installation, mounting

Mounting type	flush-mounted
Installation mode	for catch fixing

Connection

Type of load	universal
Conductor cross-section	1.5...2.5 mm ²
Type of connection	Screw connection

Equipment

Substation input	Yes
Dimming principle	phase cut-on or cut-off according to load type, self-learning

Safety

IK protection code against mechanical impacts	03
---	----

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
-------	---------