



WXF070

Connected dimmer gallery

Technical properties

Architecture

Type of control unit Push button

Main electrical features

Nominal voltage 230 V

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Power

Halogen switching capacity 230V 20 / 275 W

Incandescent bulb power 20 / 275 W

Installation, mounting

Mounting type flush-mounted

Installation mode for catch fixing

Connection

Type of load universal

Conductor cross-section 1.5...2.5 mm²

Type of connection Screw connection

Equipment

Substation input Yes

Dimming principle phase cut-on or cut-off according to load type, self-learning

Safety

IK protection code against mechanical impacts 03

REACH conform No

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery