



WXF070

Connected dimmer gallery

Technical properties

Architecture

Type of control unit Push button

Main electrical features

Nominal voltage 230 V
 Nominal voltage 230 V
 Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Power

Halogen switching capacity 230V 20 / 275 W
 Incandescent bulb power 20 / 275 W

Installation, mounting

Mounting type flush-mounted
 Installation mode for catch fixing

Connection

Type of load universal
 Conductor cross-section 1.5...2.5 mm²
 Type of connection Screw connection

Equipment

Substation input Yes
 Dimming principle phase cut-on or cut-off according to load type, self-learning

Safety

IK protection code against mechanical impacts 03
 REACH conform No
 RoHS conform Yes
 Halogen free No

Use conditions

Operating temperature -10...35 °C
 Storage/transport temperature -10...50 °C

Identification

Range gallery