



WXF070

Connected dimmer gallery

Technical properties

Α.			cti	
AI	rcn	пте	CTL	ıre

Architecture	
Type of control unit	Push button
Main electrical features	
Nominal voltage	230 V
Nominal voltage	230 V
Frequency	50 Hz
Voltage	
Operating voltage	230 V AC
Power	
Halogen switching capacity 230V	20 / 275 W
Incandescent bulb power	20 / 275 W
Installation, mounting	
Mounting type	flush-mounted
Installation mode	for catch fixing
Connection	
Type of load	universal
Conductor cross-section	1.52.5 mm²
Type of connection	Screw connection
Equipment	
Substation input	Yes
Dimming principle	phase cut-on or cut-off according to load type, self- learning
Safety	
IK protection code against mecanical impacts	03
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-1035 °C
Storage/transport temperature	-1050 °C
Identification	
Range	gallery