



WXF070

**Connected dimmer gallery**

**Technical properties**

**Architecture**

Type of control unit Push button

**Main electrical features**

Nominal voltage 230 V  
 Nominal voltage 230 V  
 Frequency 50 Hz

**Voltage**

Operating voltage 230 V AC

**Power**

Halogen switching capacity 230V 20 / 275 W  
 Incandescent bulb power 20 / 275 W

**Materials**

Material Polycarbonate (PC)

**Installation, mounting**

Mounting type flush-mounted  
 Installation mode for catch fixing

**Connection**

Type of load universal  
 Conductor cross-section 1.5...2.5 mm<sup>2</sup>  
 Type of connection Screw connection

**Equipment**

Substation input Yes  
 Dimming principle phase cut-on or cut-off according to load type, self-learning

**Safety**

IK protection code against mechanical impacts 03

**Use conditions**

Operating temperature -10...35 °C  
 Storage/transport temperature -10...50 °C

**Identification**

Range gallery