



WXF102

## Socket gallery 2P

### Technical properties

#### Architecture

Type of order	Socket
Fixing mode	Clipped

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Depth	35.65 mm
Height	45 mm
Width	45 mm

#### Materials

Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
-------	---------

