



WXF102

Socket gallery 2P

Technical properties

Architecture

| | |
|---------------|---------|
| Type of order | Socket |
| Type of pole | 2 P |
| Fixing mode | Clipped |

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|--------|----------|
| Depth | 35.65 mm |
| Height | 45 mm |
| Width | 45 mm |

Materials

| | |
|---------------------------|-----------|
| Surface appearance | matt |
| Type of surface treatment | untreated |

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm ² |
| Connection cross-sect. rigid cable | 1,5 / 2,5mm ² |
| Type of connection | Quickconnect |

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | Enhanced contact protection |

Use conditions

| | |
|-------------------------------|--------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |
| Identification | |
| Range | gallery |
| Composition | Middle plate |