



WXF102

Socket gallery 2P

Technical properties

Architecture

Type of pole	2 P
Fixing mode	Clipped

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	35.65 mm
Height	45 mm
Width	45 mm

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C