



WXF105

**Socket gallery refurbishing 2P+E**

**Technical properties**

**Architecture**

Type of order	Socket
Type of pole	2P+T
Fixing mode	Clipped

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Nominal voltage	250 V
-----------------	-------

**Dimensions**

Depth	35.85 mm
Height	45 mm
Width	45 mm

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	NFC 61314
-----------	-----------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection

**Use conditions**

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature

-10...50 °C

**Identification**

---

Composition

Middle plate