



WXF105

Socket gallery refurbishing 2P+E

Technical properties

Architecture

Type of pole	2P+T
Fixing mode	Clipped

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Dimensions

Depth	35.85 mm
Height	45 mm
Width	45 mm

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	matt
Type of surface treatment	untreated

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NFC 61314
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature

-10...50 °C

Identification

Composition

Middle plate