



WXF105

## Socket gallery refurbishing 2P+E

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Number of modules 2

#### Main electrical features

Nominal voltage 250 V

#### Dimensions

Depth 35.85 mm

Height 45 mm

Width 45 mm

#### Materials

Colour dark grey

RAL colour RAL 7011 - Iron grey

Surface appearance matt

Type of surface treatment untreated

#### Connection

Type of connection Quickconnect

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE concerned

#### Safety

IK protection code against mechanical impacts 05

Protection Enhanced contact protection

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Composition Middle plate