



WXF112

USB charger gallery

Technical properties

Connectivity

Connectors / jacks with 2 USB sockets type A

Main electrical features

| | |
|-------------------------------|-------------|
| Rated voltage | 200...250 V |
| Efficiency at low load (10 %) | 74.1 % |
| Average active efficiency | 83.3 % |
| Frequency | 50/60 Hz |

Voltage

| | |
|----------------|----------|
| Input voltage | 230 V AC |
| Output voltage | 5 V |

Electric current

| | |
|----------------|-----|
| Output current | 3 A |
|----------------|-----|

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Power

| | |
|---------------------------|-------|
| Output power | 15 W |
| No-load power consumption | 71 mW |

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 7021 - Black grey |
|------------|-----------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...35 °C |
|-----------------------|------------|

Instructions

| | |
|------------------|--------------------------------|
| Information text | No data transmission possible! |
|------------------|--------------------------------|