



WXF112

USB charger gallery

Technical properties

Connectivity

Connectors / jacks with 2 USB sockets type A

Main electrical features

Rated voltage	200...250 V
Efficiency at low load (10 %)	74.1 %
Average active efficiency	83.3 %
Frequency	50/60 Hz

Voltage

Input voltage	230 V AC
Output voltage	5 V DC
Output voltage	5 V

Electric current

Output current	3 A
----------------	-----

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Power

Output power	15 W
No-load power consumption	71 mW

Use conditions

Operating temperature	-5...35 °C
-----------------------	------------

Instructions

Information text No data transmission possible!