



WXF160B

Schuko socket gallery 2P+E pure-white

Technical properties

Architecture

| | |
|---------------|---------|
| Type of order | Socket |
| Type of pole | SCHUKO |
| Fixing mode | Clipped |

Configuration

| | |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|--------|----------|
| Depth | 40.25 mm |
| Height | 45 mm |
| Width | 45 mm |

Cover, door

| | |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

Materials

| | |
|------------------------------|-----------|
| Free area for finishing name | pure |
| Colour | white |
| Surface appearance | glossy |
| Type of surface treatment | untreated |
| Metallic colour | No |

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm ² |
| Connection cross-sect. rigid cable | 1,5 / 2,5mm ² |
| Type of connection | Quickconnect |

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|-----|
| Approvals | VDE |
|-----------|-----|

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | Enhanced contact protection |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

Identification

| | |
|-------------|-----------------------------|
| Range | gallery |
| Composition | Mechanism with upper casing |
