



WXF160D

Schuko socket gallery 2P+E dune

Technical properties

Architecture

Fixing mode Clipped

Configuration

Number of modules 6

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth 40.25 mm

Height 45 mm

Width 45 mm

Cover, door

Cover Complete housing

Materials

Free area for finishing name dune

RAL colour RAL 1013 - Oyster white

Material Polycarbonate (PC)

Type of surface treatment untreated

Metallic colour No

Connection

Type of connection Quickconnect

Equipment

With transparent product label holder No

Standards

Approvals VDE

European directive WEEE concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------