



WXF160E

**Schuko socket gallery 2P+E orange**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Number of modules	6
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	40.25 mm
Height	45 mm
Width	45 mm

**Cover, door**

Cover	Complete housing
-------	------------------

**Materials**

Free area for finishing name	orange
Colour	orange
Type of surface treatment	untreated
Metallic colour	No

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	05
Protection	Enhanced contact protection

**Use conditions**

Operating temperature

-10...35 °C

**Identification**

---

Range

gallery

---

Composition

Mechanism with upper casing