



WXF160N

**Schuko socket gallery 2P+E night**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Number of modules 6

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Depth 40.25 mm

Height 45 mm

Width 45 mm

**Cover, door**

Cover Complete housing

**Materials**

Free area for finishing name night

Colour deep black

RAL colour RAL 9005 - Jet black

Type of surface treatment Painted

Metallic colour No

**Connection**

Type of connection Quickconnect

**Equipment**

With transparent product label holder No

**Standards**

European directive WEEE concerned

**Safety**

IK protection code against mechanical impacts 05

Protection Enhanced contact protection

**Use conditions**

---

Operating temperature

-10...35 °C

**Identification**

---

Range

gallery

Composition

Mechanism with upper casing