



WXF160N

## Schuko socket gallery 2P+E night

### Technical properties

#### Architecture

Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Clipped

#### Configuration

Number of modules	6
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Depth	40.25 mm
Height	45 mm
Width	45 mm

#### Cover, door

Cover	Complete housing
-------	------------------

#### Materials

Free area for finishing name	night
Surface appearance	satin finish
Metallic colour	No

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	VDE
-----------	-----

#### Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
<b>Use conditions</b>	
Operating temperature	-10...35 °C
<b>Identification</b>	
Range	gallery
Composition	Mechanism with upper casing