



WXF160V

Schuko socket gallery 2P+E green

Technical properties

Architecture

Fixing mode Clipped

Configuration

Number of modules 6

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth 40.25 mm

Height 45 mm

Width 45 mm

Cover, door

Cover Complete housing

Materials

Free area for finishing name green

Colour green

Type of surface treatment untreated

Metallic colour No

Connection

Type of connection Quickconnect

Equipment

With transparent product label holder No

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts 05

Protection Enhanced contact protection

Use conditions

Operating temperature

-10...35 °C

Identification

Range

gallery

Composition

Mechanism with upper casing