



WXF160V

Schuko socket gallery 2P+E green

Technical properties

Architecture	
Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Clipped
Configuration	
Number of modules	6
Main electrical features	
Nominal voltage	250 V
Frequency	50/60 Hz
Electric current	
Rated current	16 A
Dimensions	
Depth	40.25 mm
Height	45 mm
Width	45 mm
Cover, door	
Cover	Complete housing
Materials	
Free area for finishing name	green
Surface appearance	glossy
Type of surface treatment	untreated
Metallic colour	No
Connection	
Connection cross-sect. flexible conductor	1,5 / 2,5mm²
Connection cross-sect. rigid cable	1,5 / 2,5mm²
Type of connection	Quickconnect
Equipment	
With transparent product label holder	No
Standards	
Approvals	VDE

Safety

IK protection code against mecanical	
impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
Use conditions	
Operating temperature	-1035 °C
Identification	
Range	gallery
Composition	Mechanism with upper casing