



WXF165B

Schuko socket gallery with lid 2P+E pure-white

Technical properties

Architecture

Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Screwed

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	43.35 mm
Height	45 mm
Width	45 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Free area for finishing name	pure
Colour	white
RAL colour	RAL 9016 - Traffic white
Material	Polycarbonate (PC)
Surface appearance	glossy
Type of surface treatment	untreated
Metallic colour	No

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals

VDE

European directive WEEE

concerned

Safety

IK protection code against mechanical impacts

05

Protection index IP

IP21

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Protection

Enhanced contact protection

Use conditions

Operating temperature

-10...35 °C

Identification

Range

gallery

Composition

Mechanism with upper casing