



WXF165N

Schuko socket gallery with lid 2P+E night

Technical properties

Architecture

Type of order	Socket
Type of pole	SCHUKO

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	43.35 mm
Height	45 mm
Width	45 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Free area for finishing name	night
Surface appearance	satın finish
Metallic colour	No

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	VDE
-----------	-----

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes

RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Identification

Range	gallery
Composition	Mechanism with upper casing