



WXF165T

**Schuko socket gallery with lid 2P+E titane**

**Technical properties**

**Architecture**

Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Screwed

**Configuration**

Number of modules	6
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	43.35 mm
Height	45 mm
Width	45 mm

**Cover, door**

Cover	Complete housing
-------	------------------

**Materials**

Free area for finishing name	titane
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	Polycarbonate (PC)
Surface appearance	satın finish
Type of surface treatment	Painted
Metallic colour	Yes

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals

VDE

European directive WEEE

concerned

---

**Safety**

IK protection code against mechanical impacts

05

Protection index IP

IP21

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Protection

Enhanced contact protection

---

**Use conditions**

Operating temperature

-10...35 °C

---

**Identification**

Range

gallery

Composition

Mechanism with upper casing