



WXF224

## RJ45 socket gallery cat.6 FTP

### Technical properties

#### Architecture

|      |     |
|------|-----|
| Type | FTP |
|------|-----|

#### Connectivity

|        |                      |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

#### Dimensions

|       |         |
|-------|---------|
| Depth | 34.6 mm |
|-------|---------|

|        |       |
|--------|-------|
| Height | 45 mm |
|--------|-------|

|       |       |
|-------|-------|
| Width | 45 mm |
|-------|-------|

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

#### Materials

|                              |      |
|------------------------------|------|
| Free area for finishing name | noir |
|------------------------------|------|

|                    |      |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

#### Connection

|                                    |                            |
|------------------------------------|----------------------------|
| Connection cross-sect. rigid cable | 0,5 - 0,65 mm <sup>2</sup> |
|------------------------------------|----------------------------|

|                |                               |
|----------------|-------------------------------|
| Connector type | shielding connection via Clip |
|----------------|-------------------------------|

#### Cable

|           |           |
|-----------|-----------|
| AWG range | AWG 26-22 |
|-----------|-----------|

#### Safety

|   |      |
|---|------|
| IK protection code against mechanical impacts | IK02 |
|---|------|

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|            |   |
|------------|---|
| Protection | with optional dust protection hinged covers |
|------------|---|

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

|                               |             |
|-------------------------------|-------------|
| Storage/transport temperature | -10...50 °C |
|-------------------------------|-------------|

#### Identification

|                    |                          |
|--------------------|--------------------------|
| Application, usage | Communication technology |
|--------------------|--------------------------|

|       |         |
|-------|---------|
| Range | gallery |
|-------|---------|

|             |              |
|-------------|--------------|
| Composition | Middle plate |
|-------------|--------------|