



WXF224

**RJ45 socket gallery cat.6 FTP**

**Technical properties**

**Architecture**

Type	FTP
Fixing mode	flush-mounting

**Connectivity**

Outlet	with straight outlet
--------	----------------------

**Dimensions**

Depth	34.6 mm
Height	45 mm
Width	45 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	noir
Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	mat

**Cable**

AWG range	AWG 26-22
-----------	-----------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
Protection	with optional dust protection hinged covers

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Application, usage	Communication technology
Range	gallery
Composition	Middle plate