



WXF225

RJ45 socket gallery cat.6 UTP

Technical properties

Architecture

Type UTP

Connectivity

Outlet with straight outlet

Dimensions

Depth 34.6 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Surface appearance matt

Connection

Connection cross-sect. rigid cable 0,5 - 0,65 mm²

Connector type shielding connection via Clip

Cable

AWG range AWG 26-22

Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Protection with optional dust protection hinged covers

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Application, usage Communication technology

Range gallery

Composition Middle plate