



WXF228

## RJ45 socket gallery cat.6A STP

### Technical properties

#### Architecture

Type	STP
Fixing mode	flush-mounting

#### Connectivity

Outlet	with straight outlet
--------	----------------------

#### Dimensions

Depth	38 mm
Height	45 mm
Width	45 mm

#### Attenuation

Transmission loss	3 dB
-------------------	------

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	matt

#### Cable

AWG range	AWG 26-22
-----------	-----------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
Protection	with optional dust protection hinged covers

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Application, usage	Communication technology
Range	gallery

