



WXF228

RJ45 socket gallery cat.6A STP

Technical properties

Architecture

| | |
|------|-----|
| Type | STP |
|------|-----|

Connectivity

| | |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

Dimensions

| | |
|-------|-------|
| Depth | 38 mm |
|-------|-------|

| | |
|--------|-------|
| Height | 45 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 45 mm |
|-------|-------|

Attenuation

| | |
|-------------------|------|
| Transmission loss | 3 dB |
|-------------------|------|

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

Connection

| | |
|------------------------------------|----------------------------|
| Connection cross-sect. rigid cable | 0,5 - 0,65 mm ² |
|------------------------------------|----------------------------|

| | |
|----------------|-------------------------------|
| Connector type | shielding connection via Clip |
|----------------|-------------------------------|

Cable

| | |
|-----------|-----------|
| AWG range | AWG 26-22 |
|-----------|-----------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK02 |
|---|------|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|------------|---|
| Protection | with optional dust protection hinged covers |
|------------|---|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -10...50 °C |
|-------------------------------|-------------|

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
|--------------------|--------------------------|

| | |
|-------|---------|
| Range | gallery |
|-------|---------|

| | |
|-------------|--------------|
| Composition | Middle plate |
|-------------|--------------|