



WXF230

**RJ45 socket gallery cat.6 UTP 2 modules 45° inside**

**Technical properties**

**Architecture**

Type FTP

**Connectivity**

Outlet with 45° oblique outlet

**Dimensions**

Depth 34.6 mm

Height 45 mm

Width 45 mm

**Capacity**

Number of sockets 1

**Materials**

Surface appearance matt

**Connection**

Connection cross-sect. rigid cable 0,5 - 0,65 mm<sup>2</sup>

Connector type shielding connection via Clip

**Cable**

AWG range AWG 26-22

**Safety**

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Protection with optional dust protection hinged covers

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Application, usage Communication technology

Range gallery

Composition Middle plate