



WXF232

RJ45 socket gallery cat.6 STP 2 modules 45° inside

Technical properties

Architecture

Type	UTP
Fixing mode	flush-mounting

Connectivity

Outlet	with 45° oblique outlet
--------	-------------------------

Dimensions

Depth	34.6 mm
Height	45 mm
Width	45 mm

Attenuation

Transmission loss	3 dB
-------------------	------

Capacity

Number of sockets	1
-------------------	---

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	matt

Cable

AWG range	AWG 26-22
-----------	-----------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
Protection	with optional dust protection hinged covers

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Application, usage	Communication technology
Range	gallery

