



WXF251

### TV socket gallery passthrough BNC socket 10 db 2 modules

#### Technical properties

##### Connectivity

Passband	4 - 862 MHz
----------	-------------

##### Dimensions

Depth	34 mm
Height	45 mm
Width	45 mm

##### Capacity

Number of sockets	1
-------------------	---

##### Materials

Surface appearance	matt
Type of surface treatment	untreated

##### Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

##### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

##### Identification

Range	gallery
Composition	Middle plate