



WXF251

TV socket gallery passthrough BNC socket 10 db 2 modules

Technical properties

Architecture

Fixing mode flush-mounting

Connectivity

Passband 4 - 862 MHz

Dimensions

Depth 34 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Material Plastic/metal

Surface appearance matt

Type of surface treatment untreated

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C