



WXF256

TV + FM+ SAT socket gallery triple 1 cable direct 2 modules

Technical properties

Connectivity

Passband	4 - 2400 MHz
----------	--------------

Dimensions

Depth	34 mm
Height	45 mm
Width	45 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	matt
Type of surface treatment	untreated

Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Middle plate