



WXF257

**TV + FM+ SAT socket gallery triple 2 cables direct 2 modules**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Connectivity**

Passband 4 - 2400 MHz

**Dimensions**

Depth 34 mm

Height 45 mm

Width 45 mm

**Capacity**

Number of sockets 1

**Materials**

Material Plastic/metal

Surface appearance matt

Type of surface treatment untreated

**Standards**

European directive WEEE concerned

**Safety**

IK protection code against mechanical impacts IK02

Protection index IP IP20

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition Middle plate