



WXF258

TV socket gallery type F direct 2 modules

Technical properties

Architecture

Fixing mode flush-mounting

Connectivity

Passband 4 - 2400 MHz

Dimensions

Depth 34 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Material Plastic/metal

Surface appearance matt

Type of surface treatment untreated

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Middle plate