



WXF259

**Socket gallery TV + FM double type F direct 2 modules**

**Technical properties**

**Architecture**

Fixing mode	flush-mounting
-------------	----------------

**Connectivity**

Passband	4 - 862 MHz
----------	-------------

**Dimensions**

Depth	34 mm
Height	45 mm
Width	45 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Material	Plastic/metal
Surface appearance	matt
Type of surface treatment	untreated

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	IK02
Protection index IP	IP20

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	Middle plate